



Sample photo

Order symbol: PC 200/100 XHG
Product nbr: 6013326
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074021915
EI. number:
Finland: 3421616
Electric No. Denmark: 8212022603
Electric No. Italy: 7351145
Electric No. Sweden: 6013326

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Accessories:		
mm:	255	180	100	MIN 15	DIN-15 Mounting rail
inch:	10.0	7.1	3.9	MIN 20	DIN-15 Mounting rail
			MIV 15	DIN-35 Mounting rail	
			MIV 20	DIN-35 Mounting rail	
Materials:			FP A 200/180	Front plate (Aluminium)	
Material:	Polycarbonate		HFP 180	Front plate hinge series	
Base colour:	RAL 7035 -light grey		FP 22046	Wall fastening lug (4 pcs)	
Cover screws material:	Polyamide				
Cover colour:	RAL 7035 -light grey				
Cover screws colour:	Grey				
Gasket material:	Polyurethane				
Temperatures:			Rating:		
Temperature °C (short term):	-40 ... 120 °C		Ingress Protection (EN 60529): IP66/IP67		
Temperature °C (continuous):	-40 ... 80 °C		Impact Resistance (EN 62262): IK08		
Temperature °F (short term):	-40 ... 250 °F		Electrical insulation: Totally insulated		
Temperature °F (continuous):	-40 ... 175 °F		Halogen free (DIN/VDE 0472, Part 815): 1		
Accessories:			UV resistance: UL 508		
MIV 200	Mounting plate (Galvanized steel)		Flammability Rating: UL 746C 5"		
			Glow Wire Test (IEC 695-2-1) °C: 960		
			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13		
			Certificates:		
			Germanischer Lloyd (GL)		
			SGS Fimko		
			Gost R		

