

SOLID PC 2828 18 G



Sample photo

Order symbol: PC 2828 18 G
Product nbr: 5330372
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074005540
El. number:
Finland: 3423715
Electric No. Italy: 7401045
Electric No. Sweden: 2539420

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:			Accessories:		
mm:	278	278	180	EKOXT	Mounting plate isolated
inch:	10.9	10.9	7.1	EKV 22	DIN-35 Mounting rail
				EKOZR	Extension frame
Materials:			Rating:		
Material:	Polycarbonate		Ingress Protection (EN 60529): IP66/IP67		
Base colour:	RAL 7035 -light grey		Impact Resistance (EN 62262): IK08/IK09		
Cover screws material:	Polyamide		Electrical insulation: Totally insulated		
Cover colour:	RAL 7035 -light grey		Halogen free (DIN/VDE 0472, Part 815): 1		
Cover screws colour:	Grey		UV resistance: UL 508		
Gasket material:	Polyurethane		Flammability Rating: UL 746C 5"		
			Glow Wire Test (IEC 695-2-1) °C: 960		
			NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12		
Temperatures:			Certificates:		
Temperature °C (short term):	-40 ... 120 °C		SGS Fimko		
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 250 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
EKOVT	Mounting plate				

SOLID 278x278x130-180

