

Finishing Sanders
GSS 280AE



330W 1/2 sheet variable speed sander. Uses clamps or velcro type fixing for paper sheets. Smooth vibration free sanding. Complete with dust bag and carrying case.

Model GSS 280AE
Input Power 330 W
No Load Speed 11000 rpm
Sanding Orbits 11000-22000 rpm
Base Plate 114 x 226 mm
Weight 2.6 kg

490676

Voltage	Order Code	Price Each
230	135-8360	
110	135-8361	