

**PICCOLO ABS B 85 G**



Sample photo

**Order symbol:** ABS B 85 G  
**Product nbr:** 8784304  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074002013  
**EI. number:**  
 Finland: 3423453  
 Electric No. Denmark: 8212001828  
 Electric No. Italy: 7211015  
 Electric No. Sweden: 2536704

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	110	80	85	B-3	DIN-35 Mounting rail
inch:	4.3	3.1	3.3	FP 22040	Wall fastening lug (2 pcs)

Materials:		Rating:	
<b>Material:</b>	ABS	Ingress Protection (EN 60529): IP66/IP67	
<b>Base colour:</b>	RAL 7035 -light grey	Impact Resistance (EN 62262): IK07	
<b>Cover screws material:</b>	Polyamide	Electrical insulation: Totally insulated	
<b>Cover colour:</b>	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Cover screws colour:</b>	Grey	Flammability Rating: UL 94 HB	
<b>Gasket material:</b>	Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 650	
		NEMA Class: NEMA 1, 4X, 6, 12, 13	

Temperatures:	
<b>Temperature °C (short term):</b>	-40 ... 80 °C
<b>Temperature °C (continuous):</b>	-40 ... 60 °C
<b>Temperature °F (short term):</b>	-40 ... 175 °F
<b>Temperature °F (continuous):</b>	-40 ... 140 °F

Accessories:	
B-MP	Mounting plate

