

PICCOLO ABS C 65 T



Sample photo

Order symbol: ABS C 65 T
Product nbr: 8784005
Description: Enclosure, ABS
Remarks: Transparent cover

EAN: 6418074002068
El. number:
Finland: 3423555
Electric No. Denmark: 8212001857
Electric No. Italy: 7212020
Electric No. Sweden: 2536738

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:			Length	Width	Height
mm:			140	80	65
inch:			5.5	3.1	2.6
Materials:					
Material:			ABS		
Base colour:			RAL 7035 -light grey		
Cover screws material:			Polyamide		
Cover colour:			Clear transparent		
Cover screws colour:			Grey		
Gasket material:			Polyurethane		
Temperatures:					
Temperature °C (short term):			-40 ... 80 °C		
Temperature °C (continuous):			-40 ... 60 °C		
Temperature °F (short term):			-40 ... 175 °F		
Temperature °F (continuous):			-40 ... 140 °F		
Accessories:					
C-MP			Mounting plate		

Accessories:	
CHM-3	DIN-35 Mounting rail
FP 22040	Wall fastening lug (2 pcs)
Rating:	
Ingress Protection (EN 60529): IP66/IP67	
Impact Resistance (EN 62262): IK07	
Electrical insulation: Totally insulated	
Halogen free (DIN/VDE 0472, Part 815): 1	
Flammability Rating: UL 94 HB	
Glow Wire Test (IEC 695-2-1) °C: 650	
NEMA Class: NEMA 1, 4X, 6, 12, 13	

PICCOLO 140x80x65-85

