

**QUICK CAB PCQ 302017 G**



Sample photo

**Order symbol:** CAB PCQ 302017 G  
**Product nbr:** 8113338  
**Description:** Cabinet, PC  
**Remarks:** Grey cover

**EAN:** 6418074011145  
**EI. number:**  
 Finland: 3421970  
 Electric No. Italy: 7681020  
 Electric No. Sweden: 2539106

Including: Base with screws for mounting plate/DIN-rail, internal corner plugs, cover with PUR gasket and CS 12137 cover screws.

Dimensions:		Length	Width	Height	Accessories:		
mm:		300	200	170	EKIV 17	DIN-35 Mounting rail	
inch:		11.8	7.9	6.7	EKIV 27	DIN-35 Mounting rail	
<b>Materials:</b>						FP A 23	Swing-out door/Front plate
<b>Material:</b>		Polycarbonate			MB 12225 AL	Swing door set	
<b>Base colour:</b>		RAL 7035 -light grey			FP 12-23	Front plate	
<b>Cover screws material:</b>		Polyamide			DRF 23	DIN rail frame set	
<b>Cover colour:</b>		RAL 7035 -light grey			DRF 33	DIN rail frame set	
<b>Cover screws colour:</b>		RAL 5023			PAT 12040	Hinge set	
<b>Gasket material:</b>		Polyurethane					
<b>Temperatures:</b>						<b>Rating:</b>	
<b>Temperature °C (short term):</b>		-40 ... 120 °C			Ingress Protection (EN 60529): IP66/IP67		
<b>Temperature °C (continuous):</b>		-40 ... 80 °C			Impact Resistance (EN 62262): IK08		
<b>Temperature °F (short term):</b>		-40 ... 250 °F			Electrical insulation: Totally insulated		
<b>Temperature °F (continuous):</b>		-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1		
<b>Accessories:</b>						UV resistance: UL 508	
EKIV 23		Mounting plate			Flammability Rating: UL 746C 5"		
						Glow Wire Test (IEC 695-2-1) °C: 960	
						NEMA Class: NEMA 1, 4, 4X, 12, 13	
						<b>Certificates:</b>	
						Germanischer Lloyd (GL)	
						SGS Fimko	
						Lloyds Register of Shipping (LR)	
						Gost R	

