



Sample photo

**Order symbol:** PC 162513  
**Product nbr:** 7032860  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074003690  
**EI. number:**  
 Finland: 3423442  
 Electric No. Denmark: 8212002966  
 Electric No. Italy: 7301055  
 Electric No. Sweden: 2536131

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:	Length	Width	Height	Rating:
mm:	250	160	125	Ingress Protection (EN 60529): IP66/IP67
inch:	9.8	6.3	4.9	Impact Resistance (EN 62262): IK07/IK08
<b>Materials:</b>				Electrical insulation: Totally insulated
<b>Material:</b>	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
<b>Base colour:</b>	RAL 7035 -light grey			UV resistance: UL 508
<b>Cover screws material:</b>	Stainless steel			Flammability Rating: UL 746C 5"
<b>Cover colour:</b>	RAL 7035 -light grey			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Gasket material:</b>	Polyurethane			NEMA Class: NEMA 1, 4, 4X, 12, 13
<b>Temperatures:</b>				<b>Certificates:</b>
<b>Temperature °C (short term):</b>	-40 ... 120 °C			SGS Fimko
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Gost R
<b>Temperature °F (short term):</b>	-40 ... 250 °F			
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			

