



Sample photo

Order symbol: PCT 071004
Product nbr: 7022531
Description: Enclosure, PC
Remarks: Clear transparent cover

EAN: 6418074058515
El. number:
Finland: 3435382
Electric No. Denmark: 8212002555
Electric No. Sweden: 7022531

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm:	98	66	41	Ingress Protection (EN 60529): IP66/IP67
inch:	3.9	2.6	1.6	Impact Resistance (EN 62262): IK07/IK08
				Electrical insulation: Totally insulated
Materials:				Halogen free (DIN/VDE 0472, Part 815): 1
Material:	Polycarbonate			UV resistance: UL 508
Base colour:	RAL 7035 -light grey			Flammability Rating: UL 746C 5"
Cover screws material:	Stainless steel			Glow Wire Test (IEC 695-2-1) °C: 960
Cover colour:	Clear transparent			NEMA Class: NEMA 1, 4, 4X, 12, 13
Gasket material:	Polyurethane			
Temperatures:				Certificates:
Temperature °C (short term):	-40 ... 120 °C			Gost R
Temperature °C (continuous):	-40 ... 80 °C			
Temperature °F (short term):	-40 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			

EURONORD PC/ABS 98x66x41

