

CARDMASTER PC 17/16-LFC3



Order symbol: PC 17/16-LFC3
Product nbr: 7520204
Description: Enclosure, PC
Remarks: Grey screw cover

EAN: 6418074010247
El. number:
Finland: 3438224
Electric No. Sweden: 7520204

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:				Accessories:	
mm:	166	160	89	FP 17/16	Front plate (aluminium)
inch:	6.5	6.3	3.5	FC PC 17/16	Frame of PC front plate
Materials:				Rating:	
Material:	Polycarbonate			Ingress Protection (EN 60529): IP65	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07/IK08	
Gasket material:	EPDM & PUR			Electrical insulation: Totally insulated	
Temperatures:				Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °C (short term):	-40 ... 120 °C			UV resistance: UL 508	
Temperature °C (continuous):	-40 ... 80 °C			Flammability Rating: UL 746C 5"	
Temperature °F (short term):	-40 ... 250 °F			Glow Wire Test (IEC 695-2-1) °C: 960	
Temperature °F (continuous):	-40 ... 175 °F			NEMA Class: NEMA 1, 3, 3R, 4X, 12, 13	
Accessories:				Certificates:	
MP 17/16				SGS Fimko	
Mounting plate				Gost R	

CARDMASTER 166x160x80-106

