

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Hand and Head Torches
Catalogue number	9410, 9505, 9510, 9520, 9610, 9620, 9530R, 9540R, 9620R, 9710R, 9621
Date	08/08/2017

<p>Range Description Hand and Head Torches</p>	
<p>Features</p> <p>9510</p> <ul style="list-style-type: none"> • High power 120 lumen CREE XR-E Q5 LED • 3 lighting modes: High, Dimmed, Flash • One-handed Rapid Slide Focus mechanism (RSF) - Spot (x1) to Flood (x10) • Beam intensifying plano-convex optical lens • Robust high grade aluminium body • Water & dirt resistant, certified to IPX4 • Battery life: High - 6hrs, Dimmed - 16hrs • Battery 3 x AAA (Not supplied) 	
<p>9520</p> <ul style="list-style-type: none"> • High power 150 lumen CREE XR-E Q5 LED • 3 lighting modes: High, Dimmed, Flash • One-handed Rapid Slide Focus mechanism (RSF) - Spot (x1) to Flood (x30) • Beam intensifying plano-convex optical lens • Robust high grade aluminium body • Water & dirt resistant, certified to IPX4 • Battery life: High - 5hrs, Dimmed - 14hrs • Battery 3 x AAA (Not supplied) 	

T9505

- High power 100 lumen CREE XP-E R3 LED
- 3 lighting modes: high, dimmed, flash
- One-handed rapid slide focus mechanism – Spot (x1) to Flood (x6)
- Beam intensifying plano-convex optical lens
- Robust high grade aluminium body
- Water & dirt resistant, certified to IPX4
- Battery life: High – 3hrs, Dimmed – 7hrs
- Size: 98 x 26mm



T9530R

- High power 300 lumen CREE XM-L T6 LED
- 3 lighting modes: high, dimmed, flash
- One-handed rapid slide focus mechanism – Spot (x1) to Flood (x6)
- Beam intensifying plano-convex optical lens
- Robust high grade aluminium body
- Water & dirt resistant, certified to IPX4
- Battery life: High – 3.5hrs, Dimmed – 8hrs
- Size: 131 x 34mm



T9540R

- High power 400 lumen CREE XM-L T6 LED
- 3 lighting modes: high, dimmed, flash
- Compound spot & flood beam
- Extra large 40mm aluminium reflector
- Robust high grade aluminium reflector
- Water & dirt resistant, certified to IPX4
- Battery life: High – 3.5hrs, Dimmed – 7hrs
- Size: 235 x 55mm



T9410

- 8 Super bright LEDs
- Wide flood beam
- 180° rotating magnetic pocket clip
- Water & dirt resistant, certified to IPX4
- Battery life: 8hrs
- Size: 160 x 26mm

**T9710R**

- High performance 600 Lumen Epistar COB LED
- Power: 10W
- Wide 120° flood beam
- Magnetic base
- Vertical and horizontal rotation
- Water & dirt resistant, tested to IP65
- Battery life: 3hrs
- Size: 147 x 168 x 240mm

**T9621**

- High Power 200 Lumen Cree XM-L T6 LED
- 3 Lighting modes: high, dimmed, flash
- One-handed rapid slide focus mechanism - spot (x1) to flood (x7)
- Beam intensifying plano-convex optical lens
- Robust high-grade aluminium body
- Adjustable head lamp swivels through 90°
- Water & dirt resistant, tested to IPX4
- Battery life: high - 4hrs, dimmed - 10hrs



Item Number	Item Description	EAN No	Commodity code	Carton Qty
T9510	C.K CREE LED Hand Torch 120 Lumens	5013969977448	85131000	6
T9520	C.K CREE LED Hand Torch 150 Lumens	5013969977431	85131000	6
T9505	C.K CREE LED Hand Torch 100 Lumens	5013969977523	85131000	6
T9530R	C.K CREE LED Hand Torch 300 Lumens	5013969977530	85131000	6
T9540R	C.K CREE LED Hand Torch 400 Lumens	5013969977547	85131000	6
T9410	C.K LED Pocket Inspection Light 120 Lumens	5013969977479	85131000	12
T9710R	C.K Rechargeable LED Flood Light 600 Lumens	5013969977493	9405403960	1
T9621	LED Head Torch 200 Lumens	5013969978988	85131000	6

Technical product information		T9510	T9520			
	Body material	Aluminium Alloy	Aluminium Alloy			
	LED lifetime	100,000hrs	100,000hrs			
	Maximum range	250m	150m			
		T9505	T9530R	T9540R		
	Body material	Aluminium Alloy	Aluminium Alloy	Aluminium Alloy		
	LED lifetime	100,000hrs	100,000hrs	100,000hrs		
	Maximum range	80m	250m	350m		
		T9410	T9710R	T9621		
	Body material	Plastic	Aluminium Alloy	Aluminium Alloy		
	LED lifetime	100,000hrs	100,000hrs	100,000hrs		
	Maximum range	1m	-	200m		
	Standards compliance	None applicable				
	User health and safety information	None applicable				
	RoHS/WEEE compliance	This product range is fully Compliant with the RoHS and WEEE regulations				
Material safety data	None applicable					
Warranty	C.K Torch products are guaranteed for 3 years against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered					
Country of origin	China					

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T9510	40	40	133	169	160	125	40	138
T9520	30	30	107	104	205	135	55	223
T9505	25	97	30	80	123	27	177	86
T9530R	33	139	38	280	158	54	205	362
T9540R	55	232	53	516	182	67	330	657
T9410	15	160	34	59	107	40	235	60
T9710R	140	240	70	1168	215	120	120	1283
T9621	-	-	-	129	131	205	105	180

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T9510	160	140	200	69		
T9520	180	180	220	94		
T9505	130	190	145	64		
T9530R	165	215	420	181		
T9540R	193	350	510	282		
T9410	240	270	115	121		
T9710R	215	120	120	1283		
T9621	255	395	140	1260		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T9510	23	Clamshell	10	Card			50	box
T9520	31	Clamshell	10	Card			60	box
T9505	19	Clamshell	11	Card			64	box
T9530R	64	Clamshell	15	Card			181	box
T9540R	111	Clamshell	27	Card			282	box
T9410	19	Clamshell	7	Card			121	box
T9710R	99	Box	8	Card			1283	Box
T9621		Clamshell		Card			180	Box

Document History:
Created Date 27/08/2014
Amended 14/10/2015 – torches and head lamps now certified to IPX4