



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

IEC Exposed Welded Tip Thermocouples with Moulded Thermocouple Plug



- Thermocouple types K, J & T
- Fast response, welded exposed junction
- 1-metre-long Teflon® PFA insulated twin-twisted lead
- 1/0.2mm conductors
- 'Moulded-on' miniature flat pin plug (water resistant)
- Temperature range -75°C to $+250^{\circ}\text{C}$
- Tolerance to IEC 584 Class 1
- Colour code to IEC 584-3
- Ideal for test & development applications

| T/C Type | Conductors | Length | Termination | +Positive tail wire | -Negative tail wire | order code |
|----------|------------|--------|---------------------|---------------------|---------------------|-------------|
| 'K' | 1/0.2mm | 1 m | Mini Plug (moulded) | Green | White | XF-1206-FAR |
| 'J' | 1/0.2mm | 1 m | Mini plug (moulded) | Black | White | XF-1205-FAR |
| 'T' | 1/0.2mm | 1 m | Mini plug (moulded) | Brown | White | XF-1207-FAR |

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com