


CABLE SPECIFICATION

SPEC NO. : RG59/U SIAMESE CCS COAXIAL CABLE

Customer No. 24-10290

Construction Item	Unit	Construction Item
Conductors	Construction	1/0.81±0.05
	Material	CU
	Filler Material	---
	O. D.	0.81±0.05
Insulators	Material	Foamed PE
	Diameter	3.70±0.01
	Average Thickness	1.44±0.05
	Colour	White
Outer Conductors	AL-PET Foil	AL-P-AL
	Type	Braid
	Material	ALMG
	Coverage	60%
	Diameter	3.80±0.15
Jacket	Material	PVC (CM)
	Diameter	6.9±0.15
	Average Thickness	1.5±0.10
	Extrusion	---
	Surface	---
	Colour	White
Power Wire	Construction	16*0.254CU
	Diameter	3.2PVC
Inking	Inking Colour	Black
	Inking	Stellar Labs SIAMESE RG59/U TYPE COAX 75OHM 20AWG 75degC 2250MHz +2C18 E188601 (UL) CM RoHS COMPLIANT
Line	Length	ft 500

CONFIGURATION:



GENERAL TOLERANCES
(UNLESS SPECIFIED)

LENGTH: X. ±1
.X ±0.2
.XX ±0.10
ANGLE: X° . ±1°
.X° ±0° 30'

Stellar Labs™

UNIT:mm	REV:		NAME	RG59/U SIAMESE COAXIAL CABLE
DRAWING	XIAOSHENG2008/10/07	S. P. NO.		
CHECK		P. O. NO.	DWG. NO.	
APPROVE		SIZE	PAGE	1/1