



Tenma 72-10385

SPECIFICATIONS

Basic Functions	Range	Best Accuracy
AC Voltage	90V-1000V	√
Frequency	50Hz/60Hz	√
Special Functions		
Vibration Indication	Cancelable	√
Beeper Indicator		√
Flashing LED Light Indicator		√
Auto Power Off	Around 3 Minutes	√
Low Battery Indication	≅ 1.8V	√
NCV Detection By	Auto Sense	√
GENERAL CHARACTERISTICS		
Power	1.5V Batteries (R03) x 2	
Product Colour	Orange and Grey	
Product Net Weight	50g	
Product Size	150 x 20mm	
Standard Accessories	Batteries	
Standard Individual Packing	Blister, English Manual	
Standard Quantity Per Carton	100pcs	
Standard Carton Measurement	485 x 255 x 470mm(0.058 CBM Per Standard Carton)	
Standard Carton Gross Weight	13kg	