


# MCM CUSTOM AUDIO

## Assembly Guide




**555-15456 - 8U**

These durable 19" equipment racks are solid steel and feature enclosed side panels with proper venting. These cases are available in three sizes, 8U, 12U, and 16U. These are heavy-duty racks with 3" casters that feature locking front wheels.

### Parts List

Cage Nuts x 38	3" Casters x 4 (2 Locking)	Wrench x 1
Screws x 54	Support Brackets x 6	Hex Key x 1
Screw Covers x 8		



Thread the 3" casters onto the bottom panel which has the externally mounted rails, tighten them with the supplied wrench

Place the side panels into the bottom panel with the holes on the bottom aligned.

Insert the screws through the bottom and thread the nuts on via the opposing side. Tighten the screws using the supplied hex key.

Place the top panel on top of the side panels with the holes on both panels aligned.

Insert the screws from the top and thread the nuts on via the opposing side. Place cap covers over the screw holes on both the top and the bottom.

Insert cage nuts from the rear of the rack rail to fit your mounting needs. (The remaining screws can be used to thread into the cage nuts for equipment mounting purposes.)

Dimensions (WxDxH): 21.6" x 17.25" x 19.3"

For more rack equipment and accessories please visit our website at [www.mcmelectronics.com](http://www.mcmelectronics.com)