

Routers
GMF 1400



1400W fixed and plunge base router in one tool. Quick clamp system for easy tool-free base conversion. Fine depth adjustment system and tool-free template guide adapter. Variable speed dial for matching speed to workpiece and task. Supplied with template guide adapter, centering cone 1/4 and 1/2in combined, dust extraction hood plunge base, dust extraction hood fixed base, 1/4in collet with nut, 1/2in collet and nut, 17mm and 30mm template guides, chip

shield plunge base, chip shield fixed base, wrenches and carry case.

Model	GMF 1400
Input Power	1400 W
No Load Speed	8000-25000 rpm
Tool Holder	1/4", 1/2"
Maximum Plunge Depth	59 mm
Weight	9.3 kg

489799

	Voltage	Order Code	Price Each
	230	135-8402	
	110	135-8401	