

# UNIVERSAL ENCLOSURES

## Comms Boxes

Low profile and deep profile plastic housings with removable end panels. Designed for communication equipment such as Wi-Fi routers.

- Stylishly designed ABS plastic case with double detachable panels
- Flame resistant ABS (UL94-V0), 30 sizes, available in off-white and dark grey
- Equipped with built-in bosses for PCB mounting
- Suitable for WiFi access points, measuring equipment, controller and communication applications

### SPECIFICATION

|                        |  |
|------------------------|--|
| Materials              | Base, top and panel UL94-V0 ABS                              |
| Protection class       | IP40   |
| Operating temperature  | -10°C to +60°C   |
| Standard colours       | Dark grey and off-white                                      |
| Standard unit includes | Base, top & panel<br>4x Self tapping screw<br>4x rubber feet |



| DARK GREY TAKACHI | OFF-WHITE TAKACHI | LENGTH | WIDTH | HEIGHT |     |
|-------------------|-------------------|--------|-------|--------|-----|
| PF10-2-7D         | PF10-2-7W         | 67mm   | 100mm | 22.5mm | NEW |
| PF10-4-7D         | PF10-4-7W         | 67mm   | 100mm | 35mm   | NEW |
| PF13-3-9D         | PF13-3-9W         | 85mm   | 125mm | 25mm   | NEW |
| PF13-4-9D         | PF13-4-9W         | 85mm   | 125mm | 40mm   | NEW |
| PF10-2-10D        | PF10-2-10W        | 100mm  | 100mm | 22.5mm | NEW |
| PF10-4-10D        | PF10-4-10W        | 100mm  | 100mm | 35mm   | NEW |
| PF15-3-10D        | PF15-3-10W        | 100mm  | 150mm | 30mm   |     |
| PF15-5-10D        | PF15-5-10W        | 100mm  | 150mm | 45mm   | NEW |
| PF18-4-12D        | PF18-4-12W        | 120mm  | 175mm | 35mm   | NEW |
| PF18-5-12D        | PF18-5-12W        | 120mm  | 175mm | 50mm   | NEW |
| PF13-3-13D        | PF13-3-13W        | 125mm  | 125mm | 25mm   | NEW |
| PF13-4-13D        | PF13-4-13W        | 125mm  | 125mm | 40mm   |     |
| PF20-4-13D        | PF20-4-13W        | 135mm  | 200mm | 40mm   |     |
| PF20-6-13D        | PF20-6-13W        | 135mm  | 200mm | 60mm   |     |
| PF20-4-20D        | PF20-4-20W        | 135mm  | 200mm | 60mm   |     |
| PF20-6-20D        | PF20-6-20W        | 135mm  | 200mm | 60mm   | NEW |
| PF10-2-15D        | PF10-2-15W        | 150mm  | 100mm | 22.5mm | NEW |
| PF10-4-15D        | PF10-4-15W        | 150mm  | 100mm | 35mm   | NEW |
| PF10-6-15D        | PF10-6-15W        | 150mm  | 100mm | 55mm   |     |
| PF15-3-15D        | PF15-3-15W        | 150mm  | 150mm | 30mm   |     |
| PF15-5-15D        | PF15-5-15W        | 150mm  | 150mm | 45mm   | NEW |
| PF24-4-17D        | PF24-4-17W        | 165mm  | 240mm | 42.5mm | NEW |
| PF24-6-17D        | PF24-6-17W        | 165mm  | 240mm | 60mm   | NEW |
| PF18-4-18D        | PF18-4-18W        | 175mm  | 175mm | 35mm   | NEW |
| PF18-5-18D        | PF18-5-18W        | 175mm  | 175mm | 50mm   | NEW |
| PF13-3-19D        | PF13-3-19W        | 190mm  | 125mm | 25mm   | NEW |
| PF13-4-19D        | PF13-4-9W         | 190mm  | 125mm | 40mm   | NEW |
| PF13-6-19D        | PF13-6-19W        | 190mm  | 125mm | 60mm   | NEW |
| PF24-4-24D        | PF24-4-24W        | 240mm  | 240mm | 42.5mm | NEW |
| PF24-6-24D        | PF24-6-24W        | 240mm  | 240mm | 60mm   | NEW |

