



P1: M-938  
P2: M-938

RE.1 2001.05.25

L - 1M, 2M, 3M, 5M, 7M, 10M, 15M, 20M, 30M, 50M



3	MOLDED PVC BLACK		M304
2	RG58A/U, BRAID 112%, OD 5.0, JACKET BLACK		M304
1	BNC MALE	2	M440
No.	DESCRIPTION	Q'TY	Supplier
APPROVED	<b>RG58-xxx</b>		Cable Length Tolerances: 0 ~0.2M ±0.01M 0.21~1.0M ±0.02M 1.1 ~1.5M ±0.025M 1.51~2.1M ±0.03M 2.1M ↑ ±0.04M
CHECKED 譚小瓊			
DRAWING 鄭康華			