

# 70 06 180 T

## Diagonal Cutter with tether attachment point



- The indispensable diagonal cutter for all-round use
- High quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting-edge tips
- Cutting edges additionally induction hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- Vanadium electric steel, forged, multi stage oil-hardened
- Pliers with integrated, insulated tether attachment point for a tool tether

<b>Article No.</b>	70 06 180 T
<b>EAN</b>	4003773081470
<b>Pliers</b>	chrome plated
<b>Handles</b>	
<b>Head</b>	
<b>Style</b>	0
<b>Insulation standard</b>	IEC 60900 DIN EN 60900
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	3,0
<b>Cutting capacities hard wire (diameter) Ø mm</b>	2,5
<b>Cutting capacities soft wire (diameter) Ø mm</b>	4,0
<b>Length mm</b>	180
<b>Net weight g</b>	267



Slim head style and precise cut at blade tips: Advantageous when working in confined areas

*technical change and errors excepted*