

H6,0/15



Similar to
illustration



General ordering data

Type	H6,0/15
Order No.	0124700000
Version	Wire end ferrule, uninsulated, 15 mm
GTIN (EAN)	4008190003807
Qty.	500 pc(s).
Packaging	loose

Dimensions and weights

Width	15 mm
Width (inches)	0.591 inch
Net weight	0.302 g

Technical data

Version	uninsulated
---------	-------------

Wire-end ferrules

Collar diameter (D2)	4.7 mm
Conductor cross-section	6 mm ²
Contact surface diameter (D1)	3.5 mm
L1 in mm	15 mm
Stripping length	15 mm
Wire connection cross section AWG, max.	AWG 10

Downloads

Brochure/Catalogue

CAT 6 TOOLS 15/16 EN

Engineering Data

EPLAN, WSCAD, Zuken E3.S

Classifications

ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005
ETIM 6.0	EC000005
UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01
eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01

Approvals


Approvals



ROHS

Conform


Related products:



Type: H0,34/5
 Description of article: Wire end ferrule without plastic collar
 Order No.: 1475640000

Version:
 Wire end ferrule, uninsulated, 8 mm


[PDF data sheet](#) [Add to Inquiry List](#)



Type: H0,25/5
 Description of article: Wire end ferrule without plastic collar
 Order No.: 9018910000

Version:
 Wire end ferrule, uninsulated, 5 mm


[PDF data sheet](#) [Add to Inquiry List](#)



Type: H0,5/6
Description of article: Wire end ferrule
without plastic collar
Order No.: 0282600000

Version:
Wire end ferrule, uninsulated, 6 mm


[PDF data sheet](#) [Add to Inquiry List](#)



Type: H0,5/10
Description of article: Wire end ferrule
without plastic collar
Order No.: 9004050000

Version:
Wire end ferrule, uninsulated, 10 mm


[PDF data sheet](#) [Add to Inquiry List](#)



Type: H0,75/6
Description of article: Wire end ferrule
without plastic collar
Order No.: 0282700000

Version:
Wire end ferrule, uninsulated, 6 mm


[PDF data sheet](#) [Add to Inquiry List](#)



Type: H0,75/10
Description of article: Wire end ferrule
without plastic collar
Order No.: 0542500000

Version:
Wire end ferrule, uninsulated, 10 mm

[PDF data sheet](#) [Add to Inquiry List](#)



Type: H1,0/6
Description of article: Wire end ferrule
without plastic collar
Order No.: 0372600000

Version:
Wire end ferrule, uninsulated, 6 mm

[PDF data sheet](#) [Add to Inquiry List](#)



Type: H1,0/10
Description of article: Wire end ferrule
without plastic collar
Order No.: 0282800000

Version:
Wire end ferrule, uninsulated, 10 mm


[PDF data sheet](#) [Add to Inquiry List](#)



Type: H1,5/7
Description of article: Wire end ferrule
without plastic collar
Order No.: 0372700000

Version:
Wire end ferrule, uninsulated, 7 mm

[PDF data sheet](#) [Add to Inquiry List](#)




Type: H1,5/10

Description of article: Wire end ferrule
without plastic collar
Order No.: 0186500000

Version:

Wire end ferrule, uninsulated, 10 mm

[PDF data sheet](#) [Add to Inquiry List](#)




Type: H1,5/12

Description of article: Wire end ferrule
without plastic collar
Order No.: 9004060000

Version:

Wire end ferrule, uninsulated, 12 mm

[PDF data sheet](#) [Add to Inquiry List](#)




Type: H1,5/18

Description of article: Wire end ferrule
without plastic collar
Order No.: 9004070000

Version:

Wire end ferrule, uninsulated, 18 mm

[PDF data sheet](#) [Add to Inquiry List](#)




Type: H2,5/7

Description of article: Wire end ferrule
without plastic collar
Order No.: 0373000000

Version:

Wire end ferrule, uninsulated, 7 mm

[PDF data sheet](#) [Add to Inquiry List](#)




Type: H2,5/10

Description of article: Wire end ferrule
without plastic collar
Order No.: 9004080000

Version:

Wire end ferrule, uninsulated, 10 mm

[PDF data sheet](#) [Add to Inquiry List](#)




Type: H2,5/12

Description of article: Wire end ferrule
without plastic collar
Order No.: 0186100000

Version:

Wire end ferrule, uninsulated, 12 mm

[PDF data sheet](#) [Add to Inquiry List](#)




Type: H2,5/18

Description of article: Wire end ferrule
without plastic collar
Order No.: 9004090000

Version:

Wire end ferrule, uninsulated, 18 mm


[PDF data sheet](#) [Add to Inquiry List](#)



Type: H4,0/9
 Description of article: Wire end ferrule
 without plastic collar
 Order No.: 0373100000

Version:
 Wire end ferrule, uninsulated, 9 mm


[PDF data sheet](#) [Add to Inquiry List](#)



Type: H4,0/12
 Description of article: Wire end ferrule
 without plastic collar
 Order No.: 0244100000

Version:
 Wire end ferrule, uninsulated, 12 mm


[PDF data sheet](#) [Add to Inquiry List](#)



Type: H4,0/15
 Description of article: Wire end ferrule
 without plastic collar
 Order No.: 9004100000

Version:
 Wire end ferrule, uninsulated, 15 mm


[PDF data sheet](#) [Add to Inquiry List](#)



Type: H4,0/18
 Description of article: Wire end ferrule
 without plastic collar
 Order No.: 9004110000

Version:
 Wire end ferrule, uninsulated, 18 mm

[PDF data sheet](#) [Add to Inquiry List](#)



Type: H6,0/10
 Description of article: Wire end ferrule
 without plastic collar
 Order No.: 9004120000

Version:
 Wire end ferrule, uninsulated, 10 mm

[PDF data sheet](#) [Add to Inquiry List](#)



Type: H6,0/12
 Description of article: Wire end ferrule
 without plastic collar
 Order No.: 0191900000

Version:
 Wire end ferrule, uninsulated, 12 mm

[PDF data sheet](#) [Add to Inquiry List](#)



Type: H6,0/18
 Description of article: Wire end ferrule
 without plastic collar
 Order No.: 9004130000

Version:
 Wire end ferrule, uninsulated, 18 mm

[PDF data sheet](#) [Add to Inquiry List](#)