


H1,5/20D SW ZH SV



Similar to
illustration

General ordering data

Type	H1,5/20D SW ZH SV
Order No.	9004750000
Version	Wire end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, Black
GTIN (EAN)	4008190055431
Qty.	500 pc(s).
Packaging	Multipack bag

Dimensions and weights

Width	20 mm
Width (inches)	0.787 inch
Net weight	0.2 g

Technical data

Version	Twin wire-end ferrule
---------	-----------------------

Wire-end ferrules

Collar height (A)	6.5 mm
Collar width (B)	3.6 mm
Colour code	DIN
Conductor cross-section	1.5 mm²
Contact surface diameter (D1)	2.2 mm
Contact surface length (L2)	12 mm
L1 in mm	20 mm

Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.3 mm
Stripping length	15 mm
Wire connection cross section AWG, max.	AWG 16

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S

Classifications

ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005
ETIM 6.0	EC000005
UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01
eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01

Approvals

Approvals	
ROHS	Conform
UL File Number Search	E354986

Related products:



Type: H1,5/16 ZH R SV

Order No.: 9004410000

Description of article: Twin wire end ferrule, red

Version:

Wire end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, Red

PDF data sheet

Add to Inquiry List


Type: H1,5/16D ZH SW SV

Order No.: 9004420000


Description of article: Twin wire end ferrule, black

Version:

Wire end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, Black



[PDF data sheet](#) [Add to Inquiry List](#)



Type: H1,5/20 ZH R SV Version:
Order No.: 9004920000 Wire end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, Red
Description of article: Twin wire end ferrule,
red

[PDF data sheet](#) [Add to Inquiry List](#)