


H0,75/14S W



Similar to illustration

General ordering data

Type	H0,75/14S W
Order No.	9025960000
Version	Wire end ferrule, insulated, 10 mm, 8 mm, White
GTIN (EAN)	4008190009878
Qty.	500 pc(s).
Packaging	loose

Dimensions and weights

Width	14 mm
Width (inches)	0.551 inch
Net weight	0.09 g

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	3.4 mm
Colour code	Weidmüller
Conductor cross-section	0.75 mm ²
Contact surface diameter (D1)	1.2 mm
Contact surface length (L2)	8 mm
L1 in mm	14 mm
Metal sleeve thickness (S1)	0.15 mm

Plastic collar thickness (S2)	0.25 mm
Stripping length	10 mm
Wire connection cross section AWG, max.	AWG 18

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	WSCAD

Classifications

ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005
ETIM 6.0	EC000005
UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01
eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01

Approvals

Approvals	
ROHS	Conform
UL File Number Search	E354986

Related products:

Type: H0,34/11 S TK	Version:
Order No.: 9204090000	Wire end ferrule, insulated, 6 mm, 6 mm, Turquoise
Description of article: Wire-end ferrule with plastic collar, special size, turquoise	

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H0,5/14S OR	Version:
Order No.: 9004560000	Wire end ferrule, insulated, 10 mm, 8 mm, Orange
Description of article: Wire end ferrule with plastic collar, special size, orange	

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H0,5/14S W
Order No.: 9004590000
Description of article: Wire end ferrule with plastic collar, special size, white

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, White

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H0,5/16 DS W
Order No.: 9202910000
Description of article: Wire end ferrule with plastic collar, special size, white

Version:
Wire end ferrule, insulated, 12 mm, 10 mm, White

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H 0,5/16 S OR
Order No.: 9202900000
Description of article: Wire end ferrule with plastic collar, special size, orange

Version:
Wire end ferrule, insulated, 12 mm, 10 mm, Orange

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H0,75/14TS HBL
Order No.: 9018550000
Description of article: Wire end ferrule with plastic collar, special size, light blue

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, Light Blue

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H 0,75/15 SW
Order No.: 9204240000
Description of article: Wire end ferrule with plastic collar, special size, white

Version:
Wire end ferrule, insulated, 10 mm, 9 mm, Light Blue

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H0,75/16DS GR
Order No.: 2091010000
Description of article: Wire end ferrule with plastic collar, special size, grey

Version:
Wire end ferrule, insulated, 12 mm, 10 mm, Grey

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H1,0/14S GE
Order No.: 9025970000
Description of article: Wire end ferrule with plastic collar, special size, yellow

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, Yellow

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H1,0/14S R
Order No.: 9018560000
Description of article: Wire end ferrule with plastic collar, special size, red

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, Red

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H1,0/16 DS R
Order No.: 2092480000
Description of article: Wire end ferrule with plastic collar, special size, red

Version:
Wire end ferrule, insulated, 12 mm, 10 mm, Red

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H1,5/12S R
Order No.: 9025690000
Description of article: Wire end ferrule with plastic collar, special size, red

Version:
Wire end ferrule, insulated, 8 mm, 6 mm, Red

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H1,5/14S R
Order No.: 9025980000
Description of article: Wire end ferrule with plastic collar, special size, red

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, Red

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H1,5/14S SW
Order No.: 9025240000
Description of article: Wire end ferrule with plastic collar, special size, black

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, Black

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H1,5/16 DS SW
Order No.: 2092490000
Description of article: Wire end ferrule with plastic collar, special size, black

Version:
Wire end ferrule, insulated, 12 mm, 10 mm, Black

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H2,5/12DS BL
Order No.: 9028490000
Description of article: Wire end ferrule with plastic collar, special size, blue

Version:
Wire end ferrule, insulated, 8 mm, 6 mm, Blue

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H2,5/12TS GR
Order No.: 9036200000
Description of article: Wire end ferrule with plastic collar, special size, grey

Version:
Wire end ferrule, insulated, 8 mm, 6 mm, Grey

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H2,5/14S BL
Order No.: 1333100000
Description of article: Wire end ferrule with plastic collar, special size, blue

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, Blue

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H2,5/14TS GR
Order No.: 9426770000
Description of article: Wire end ferrule with plastic collar, special size, blue

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, Grey

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H2,5/16DS BL
Order No.: 9036220000
Description of article: Wire end ferrule with plastic collar, special size, blue

Version:
Wire end ferrule, insulated, 13 mm, 10 mm, Blue

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H2,5/16 TS GR
Order No.: 9036210000
Description of article: Wire end ferrule with plastic collar, special size, grey

Version:
Wire end ferrule, insulated, 12 mm, 10 mm, Grey

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H4,0/14DS GR
Order No.: 9028520000
Description of article: Wire end ferrule with plastic collar, special size, grey

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, Grey

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H4,0/15TS OR
Order No.: 9036230000
Description of article: Wire end ferrule with plastic collar, special size, orange

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, Orange

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H 4,0/20 DS GR
Order No.: 9203630000
Description of article: Wire end ferrule with plastic collar, special size, grey

Version:
Wire end ferrule, insulated, 15 mm, 12 mm, Grey

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H 10,0/22 S EB
Order No.: 9203620000
Description of article: Wire end ferrule with plastic collar, special size, ivory

Version:
Wire end ferrule, insulated, 15 mm, 12 mm, Ivory

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H0,75/14DS GR
Order No.: 9028580000
Description of article: Wire end ferrule with plastic collar, special size, grey

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, Grey

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H35,0/30 DS RT
Order No.: 1418020000
Description of article: Wire end ferrule with plastic collar, special size, red

Version:
Wire end ferrule, insulated, 19 mm, 16 mm, Red

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H35,0/30 S BE
Order No.: 1418030000
Description of article: Wire-end ferrules with plastic collar, special size, colour beige

Version:
Wire end ferrule, insulated, 19 mm, 16 mm, Beige

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H35,0/32 DS RT
Order No.: 1418330000
Description of article: Wire end ferrule with plastic collar, special size, red

Version:
Wire end ferrule, insulated, 21 mm, 18 mm, Red

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H35,0/32 S BE
Order No.: 1418340000
Description of article: Wire-end ferrules with plastic collar, special size, colour beige

Version:
Wire end ferrule, insulated, 21 mm, 18 mm, Beige

[PDF data sheet](#) [Add to Inquiry List](#)

