


H1,5/14 R SV



Similar to illustration

General ordering data

Type	H1,5/14 R SV
Order No.	9026090000
Version	Wire end ferrule, insulated, 10 mm, 8 mm, Red
GTIN (EAN)	4008190137168
Qty.	500 pc(s).
Packaging	Multipack bag

Dimensions and weights

Width	14 mm
Width (inches)	0.551 inch
Net weight	0.124 g

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	3.5 mm
Colour code	Weidmüller
Conductor cross-section	1.5 mm ²
Contact surface diameter (D1)	1.7 mm
Contact surface length (L2)	8 mm
L1 in mm	14 mm
Metal sleeve thickness (S1)	0.15 mm

Plastic collar thickness (S2)	0.25 mm
Stripping length	10 mm
Wire connection cross section AWG, max.	AWG 16

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S

Classifications

ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005
ETIM 6.0	EC000005
UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01
eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01

Approvals

Approvals	
ROHS	Conform

Related products:

Type: H1,5/14D SW SV	Version:
Order No.: 9019430000	Wire end ferrule, insulated, 10 mm, 8 mm, Black
Description of article: Wire end ferrule with plastic collar, black	

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H1,5/16 R SV	Version:
Order No.: 9028350000	Wire end ferrule, insulated, 12 mm, 10 mm, Red
Description of article: Wire end ferrule with plastic collar, red	

[PDF data sheet](#) [Add to Inquiry List](#)