







ITEM					 PIN	 SQ. PIN	FOR CRIMPING RG TYPE CABLE
1		.255" 6.5	.213" 5.41	.187" 4.75	.068" 1.72		55, 58, 59, 62, 140, 141, 142, 210, 223, 174, 303, 400, Fiber Optic, BELDEN 8279
2	.319" 8.1	.256" 6.5	.213" 5.41		.068" 1.72		6, 59, 62, 140, 210, BELDEN 8279, 55, 58, 141, 142, 223, 303, 400, Fiber Optic.
3	.255" 6.48	.213" 5.41	.137" 3.50	.100" 2.54	.069" 1.75	.043" 1.1	59, 62, 8X, 140, 210, BELDEN 8279, 55, 58, 141, 142, 174, 223, 303, 400, Fiber Optic
4	.178" 4.52	.151" 3.84	.128" 3.25	.078" 2.00	.068" 1.72	.042" 1.07	122, 174, 179, 180, 187, 188, 195, Fiber Optic, 178, 316, BELDEN 8218.
5	.429" 10.9		.128" 3.25	.100" 2.54			8, 9, 11, 87A, 149, 165, 213, 214, 216, 225, 393, 174, 179, 187, 188, 316, BELDEN 9913
6	6 1/2" Cable Cutter for Cutting Cable Maximum .41"ø (10.5mmø)						
7	4" Coax Stripper for Stripping RG58/59/62/6/3C2V...						
8	Carry Case with foam insert fits all components						
Die sets and other components are listed for convenience of identifying and may not be ordered separately. We will accept OEM quotation requests for special crimp tool kits modified to meet your specific needs.							