



## 2MP IR Dome HD Camera

- . 1/2.7" 2MP CMOS Sensor
- . AHD/CVI/TVI/CVBS 4 IN 1
- . 3.6mm Fixed Lens
- . IR Distance max 20m
- . IP66 outdoor, OSD&UTC support



### SPECIFICATION

Model NO.	DFR15
Video Output Mode	AHD/CVI/TVI/CVBS 4 IN 1
Camera	
Image Sensor	1/2.7" 2MP CMOS Sensor
Image Resolution	2MP 1080P/ 960H
Effective Pixels	1920*1080
TV System	PAL/NTSC
Electronic Shutter	1/25s~1/50,000s , 1/30s~1/60,000s
S/N Ratio	≥50dB
Scanning System	Progressive Scan
Lens	
Focus Length	3.6mm
Focus Control	Fixed
Lens Type	Fixed
Pixels	3M Pixels
Auto Iris Support	NO

Night Vision	
Infrared LED	14μ x 18PCS
Infrared Distance	20M
IR Status	Under 10 Lux by CDS
IR Power On	CDS Auto Control
Camera Features	
Starlight	/
Day/Night	YES
OSD Menu Language	YES
White Balance	AUTO / MANUAL
Gain Control	AUTO
Noise Reduction	DNR
Picture Adjustment	YES
WDR	YES
OSD Support	YES
UTC	YES
Dip Switch	Optional
General	
Housing	Metal, IP66
Bracket	NO
Dual Voltage	NO
IR Cut Filter	YES
Heater	NO
Audio	Optional
Operation Temperature	-10℃ ~ +50℃ RH95% Max
Storage Temperature	-20℃ ~ +60℃ RH95% Max
Power Source	DC12V±10%, 550mA
Dimension	∅ 94 x 69(H) mm
Weight	400g