

SAK Series
Q 3 SAK4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	Q 3 SAK4
Order No.	0336800000
Version	SAK Series, Cross-connector, for cross-connection link, No. of poles: 3
GTIN (EAN)	4008190089795
Qty.	50 pc(s).

SAK Series
Q 3 SAK4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	18 mm	Width (inches)	0.709 inch
Height	6 mm	Height (inches)	0.236 inch
Depth	20.5 mm	Depth (inches)	0.807 inch
Net weight	7.36 g		

Material data

Material	CuSn	Colour	Grey
----------	------	--------	------

System specifications

Version	for cross-connection link	Mounting rail	none
---------	---------------------------	---------------	------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Screwed		

Dimensions

Pitch in mm (P)	6 mm
-----------------	------

Rating data

Rated current	32 A
---------------	------

Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 5.1	27-14-11-40
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

Product information

Descriptive text technical data	Current-carrying capacity up to 41 A via the cross-connection, max. 6 mm ²
---------------------------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	0336800000_15308_Q_3_SAK4_STP.stp