




Datenblatt - Fiche technique - Data sheet


11.04.5206



ROLINE VGA-Kabel HD15 ST - ST, 6,0m

ROLINE Câble HD15 M/HD15 M, 6,0m

ROLINE HQ VGA Cable, HD15, M/M, 6 m




料号	颜色	长度
11.04.5202	黑色	2000±30mm
11.04.5203	黑色	3000±30mm
11.04.5206	黑色	6000±50mm

NOTE:

- CABLE: 28AWG, UL2919, AL+B-FOIL, 3同轴+7C(26AWG), 黑色, 齿状, OD=9.0mm. PVC JACKET
- LENGTH: 2030mm
- CONNECTORS: HDB15M * 2PCS. (黑胶芯)(空9针)
- SCREW: INCH SCREW *4 (BNC螺丝).
- CONTACTS:

HDB15M	1	2	3	6	7	8	4	5	10	11	12	13	14	64
HDB15M	1	2	3	6	7	8	4	5	10	11	12	13	14	64
	红	绿	蓝	红	绿	蓝	26AWG							
	轴	轴	轴	地	地	地								
- MOLD: IBM 四方模 (内用马口铁) 马口铁要压到编织线.)
- OPEN/SHORT TEST: 100% TEST.
INSULATIONS: 2M
- ALL MUST BE ROHS COMPLIANT.



PE BAG(190*300*0.06)
+ 吊卡+条码贴纸包装

COMPANY	RLA		ITEM NO.	11.04.5202	NO	B3876	SCALE	NON
REVISION	DATE	DISCRIPTION	DRAWN BY				UNIT(MM)	
REV.A/0	2006.04.27	C6-2604080	DESIGNED BY			DRAWING NO.		
			APPROVAL BY					

Rotronic Co., Ltd.