



Datenblatt - Fiche technique - Data sheet


**11.04.5511**




ROLINE GOLD Monitorkabel DVI, ST-ST, (24+1) dual link, 1,0m

ROLINE GOLD Câble pour écran DVI, M-M, (24+1) dual link, 1,0m

ROLINE GOLD Monitor Cable, DVI (24+1), Dual Link, M/M, 1 m



**PIN Assignment**



**ELECTRICAL TEST:**

1. 100% OPEN SHORT & MIS WIRE TEST
2. CONTACT RESISTANCE: 2 OHM(MAX)
3. INSULATION RESISTANCE: 10M OHM(MIN)
4. HI-POT TEST: DC 300V/10ms

NO	DESCRIPTION	QTY	UNIT
13	Wire Clip OD:7.3mm	2	pcs
12	Ferrite core 28.5*17.5*11.5MM	2	pcs
11	DVI M TRANSPARENT DUST COVER	2	pcs
10	DVI 24# Yellow down Shell aluminum alloy laser etching DVI LOGO	2	pcs
9	DVI 24# Yellow up Shell aluminum alloy laser etching DVI LOGO	2	pcs
8	#4-40UNC 4*38.5 Gold-plated screws	4	pcs
7	TUBE BLACK : φ 1.5*22mm THICK	0.044	m
6	TUBE BLACK : φ 1.0*12mm THIN	0.168	m
5	BLACK Ø2.0*10mm THIN	0.14	m
4	45P BLACK PVC	40	g
3	TRANSPARENT PE	8	g
2	DVI(24+1) M SOLDER TYPE, GOLD PLATED SHELL, BLACK INSULATION	2	pcs
1	UL20276 (30AWG*1PR+EAM)*7C+30AWG*1PR+30AWG*3C+AEB 85%AL OD:7.3MM WITH BLACK/YELLOW NET	1	M

⊕ ⊖	TOLERANCE	
	INCHES	M/M
	.X	.015 .30
.XX	.010 .10	
.XXX	.005 .05	

**rotronic**

11.04.5511

ROLINE GOLD DVI Cable, Dual Link, M / M  
1m, black w/yellow & black nylon net

DRAWN BY		SCALE	NONE	DRAWING NO:	REV
CHECK BY		UNIT	MM		A
APPD BY		DATE	2013.07.26		1/1