

(2.00 mm) .0787"

# COST-EFFECTIVE RUGGED SOCKETS

### **SPECIFICATIONS**

For complete specifications and recommended PCB lavouts see www.samtec.com?SQW

### Insulator Material:

Black Liquid Crystal Polymer Contact Material: Phosphor Bronze

Plating: Sn or Au over 50 µ" (1.27 µm) Ni

# Current Rating (SQW/TMMH):

3.8 A per pin (2 pins powered) Voltage Rating: 281 VAC mated with TMM; 250 VAC mated with TMMH

# Operating Temp Range: -55 °C to +125 °C Insertion Depth:

(2.62 mm) .103" to (5.03 mm) .198" with

## (0.38 mm) .015" wipe

Max Cycles: 100 with 10 μ" (0.25 μm) Au **RoHS Compliant:** 

Lead-Free Solderable: Yes, for -D & -D-VS (Wave only for -T, -Q, -5 & -6) SMT Lead Coplanarity: (0.15 mm) .006" max

**PROCESSING** 

### **RECOGNITIONS**

For complete scope of recognitions see www.samtec.com/quality







**Board Mates:** TMMH, TMM,

MTMM, MMT, TW, TSH, LTMM, PTT

## Cable Mates:

**TCMD** 





Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice