

TECHNICAL DATA SHEET

PRO-ELEC

Flexible Conduit Contractor Pack

Specification	
Material	Polypropylene
Standard	EN50086.1 EN50086.22 superseded by EN61386.1 and EN61386.22
Colour	Black
Compression resistance	Class 2 = Light 320N on 5cm at 20°C
Impact resistance	Class 2 = Light 1 Joule at 5°C
IP Rating	IP40
Min temp installation & application	-5°C
Max temp installation & application	+90°C

Code	Description	Pack QTY
ACP20BLK	Flex Con Contractor Pk 20mm	10mtrs
ACP25BLK	Flex Con Contractors Pk 25mm	10mtrs

Important Notice : This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.

PRO-ELEC