

Pallet quantity:

GE Lighting


Specification Sheet 09-09-02

Biax Extra Mini™ 11W B22 2700K

Product code: 10620 Description: FLE11TBX/XM/827 B22 220-240V LBX 1/6

Outline

Max.Overall Length, (A) :	114 mm		
Max Overall Diameter, (B):			
Max Plastic, Base Height ,(C): Max Glass Length,(D):			
Base type:			
Mass of lamp:			
	-		
Operating Conditions			
Burning position: Luminaire characteristics:	any Indoor open/enclosed		
Dimmability :	nondimmable		
Electrical Data	N 1 1		
	Nominal	Min.	Max.
Lamp Watts: Lamp Volts:	11 W 230 V	220 V	240V
Lamp Amps:			85mA
Input Frequency: THD:	50/60Hz		170%
Photometric Data			
	Nominal	Min.	Max.
Initial Lumens (VBU):	600 Lm		
Initial Lumens (VBD):	510 lm		
Average Lated Life	15,000 Hours		
Number of Starts	30,000 cycles		
Infant mortality within 1000h			1%
Lumen Maintenance @ 2000h	90%		88%
Correlated Colour Temperature (CCT):	2,700 K		
Colour Rendering Index (Ra) CRI:	82		
CIE Chromaticity Coordinates:	X: 0.464		
Starting Time	Y: 0.417		1.5sec
Warm Up Time to 80%:	20 sec		
Operating Temperature Range		10°C	40°C
Starting Temperature Range		-15°C	50°C
Others			
Standard pack: Case size (length x height x width):	6 pcs mm		
EAN number:	0043168106207		
Mass of single packed lamp:	g		
Mass of case: Pallet quantity:	kg		



Note

All performance data shows approximate values based on normal operating conditions with auxiliary equipment that meets current published specifications. Data subjects to change without notice.