

<b>DOC. TYPE:</b>  <b>SPECIFICATION DATA SHEET</b>	<b>SUBJECT:</b>  <b>HALOGEN CAPSULE LAMP G9 240V 25W 1500HRS</b>	<b>DRAWING No.:</b>  <b>FILE ID.:</b>  <b>4753483</b>
--	--	---

GENERAL INFORMATION		TECHNICAL DATA	
CODE:	SKU 10809	VOLTAGE	240V
		WATTAGE	25 W
CAP:	G9	RATED WATTAGE	25 W + 8%
BULB:	UV control		
APPLICATION	GENERAL LIGHTING	RATED LUMENS	260 lm -15%
BURNING POSITION	Universal	LIFETIME	1500 hours
PERMISSIBLE PINCH TEMPERATURE	Max.350°C		
PERMISSIBLE BULB TEMPERATURE	Min.250 °C / Max. 900°C	COLOR	2900K

<p><b>DIMENSIONS (mm)</b></p> <p>min. nom. max.</p> <p>A 13.0</p> <p>B 51.0</p>	
---	--

Relevant Standards: IEC 60432, IEC 60357, IEC 60061