



ALL DIMENSION IN MM UNLESS OTHERWISE STATED : 0.= ±0.1mm 00.= ±0.2mm 000.= ±0.3mm

HEAVY POWER CO., LTD.

A Specialist Manufacturer

No.7, Lane 106, Wukung 3rd. road,
Wuke Industrial Park, Taipei Hsien,
Taiwan, R.O.C.

Tel :886-2-22983178

Fax :886-2-22983183

Scale :

Date : 2003/03/12

Housing Material: Thermoplastic, UL 94V-2 Flame retardant

Current: 30A(cULus), 24A(VDE)

Voltage: UL-600V, VDE-450V

Working Temp: 110°C

Wire Range: 12-22 AWG Solid Conductor

Stripping Length: 11mm (0.43inch)

International Approvals

UL File No.: E-113650

CE, VDE, FIMKO, KEMA, CEBEC

TITLE :

PUSH-IN WIRE CONNECTORS

PART NO. PC258

DWG NO.

PC258

PREPARED

Esther

REV.

1.0