



Ohaus Compact Scales are ideal when cost matters and dependable results are a must. These uniquely designed scales have a wide variety of applications, more than any other scale in their class. The three portable models range in capacities from 200 g to 5000 g, and are perfect for use in light production, in the field, the kitchen, the office, and more. Easy operation, long battery life, and great performance make Compact Scales a truly remarkable value.

- Sleek, low profile design
- Large high contrast display
- Energy-saving auto shut-off feature
- Battery or AC powered
- Rugged plastic construction

Specifications

Capacity (g)	200	2000	5000
Readability (g)	0.1	1	2
Repeatability (Std. Dev.) (g)	0.1	1	2
Linearity (g)	0.1	1	2
Weighing Units	g, lb:oz		
Tare Range	to capacity by subtraction		
Stabilization Time	3 seconds		
Optimum Operating Temp.	18° - 25°C		
Power	3 AA batteries (included) AC adapter (optional accessory)		
Auto shut-off	5 minutes no activity (battery operation only)		
Calibration	digital calibration from keypad		
Display (cm)	LCD (11)		
Pan Size (cm)	146 x 133		
Dimensions LxWxH (cm)	193 x 135 x 39		
Net Weight (kg)	0.47		
Item Number	CS200	CS2000	CS5000

Standard Features

Low battery indicator, overload and underload indicators, auto shut-off, rugged plastic construction, tactile feedback keypad.

Accessories

1050 ml capacity bowl, AC adapter, stainless steel pan cover, calibration masses.

Simple To Order

Contact your dealer for product availability as well as warranty information.



Ohaus UK Ltd. 64 Boston Road

Beaumont Leys Leicester LE4 1AW ENGLAND Tel.: +44 116 234 5075 Fax: +44 116 234 6706 e-mail: uksales@ohaus.com

Ohaus Europe & MEA

Im Langacher CH-8606 Greifensee Switzerland Tel.: +41-1-944 33 66 Fax: +41-1-944 32 30 e-mail: EuropeSales@Ohaus.com

With offices in Mexico, Switzerland, England, Germany, France, Spain, Italy, Poland, Russia, Japan, Korea and China

* ISO 9001 Registered Quality Management System

www.ohaus.com

80774070 © OHAUS Europe GmbH

