

Jobber Drill Sets



High speed steel. Straight shank. Right hand cutting.  
DIN 338/BS 328. Supplied in metal case.

492620

| No. of Drills | Contents             | Order Code | Price Each |
|---------------|----------------------|------------|------------|
| 25            | 1.0 - 13.0mm x 0.5mm | 137-4250   |            |
| 51            | 1.0 - 6.0mm x 0.1mm  | 147-1942   |            |
| 41            | 6.0 - 10.0mm x 0.1mm | 147-1943   |            |
| 21            | 1/16 - 3/8 x 1/64    | 147-1875   |            |
| 29            | 1/16 - 1/2 x 1/64    | 147-1876   |            |