

ESD Cutters



- Drop forged fine polished black oxidized head
- Plain jaws with spring release handle
- Chrome vanadium steel
- 2-Component handle with slip guard
- ESD Electro static discharge certified
- Length: 130mm

1496354: Cutter no bevel round head with spring

1496355: Cutter with bevel round head and spring

1496356: Cutter no bevel with lead catcher round head and spring

Cutting Capacity: wire

Size	Soft	Med/Hard
110mm	1.5mm	0.2mm
110mm	1.5mm	0.2mm
110mm	1.5mm	0.2mm

493029.492684

Size	Order Code	Price Each
110mm	149-6354	
110mm	149-6355	
110mm	149-6356	