


KEMET, OHD



General Information

Series:	OHD
Type:	Thermal Sensors
Style:	Radial
Description:	Thermal Guard
Features:	Overheating Monitoring, Simple Circuit Design, Reliable ON-OFF Operation, Compact, High Speed Response
Lead:	Wire Leads
RoHS:	Yes

Dimensions

L	18.1mm
H	5mm
T	6.7mm
LL	10mm

Packaging Specifications

Packaging:	Bulk, Tray
Packaging Quantity:	700

Specifications

Rated Temperature:	60C
Rated Temperature Tolerance:	+/-5C
Temperature Range:	+30/+130C
Voltage DC:	30 VDC MAX (Opening/Closing), 1500 VAC/1min Or 1800 VAC/1sec (Insulation Withstand Voltage, Between Terminals And Mounting Resin Surface)
Current:	0.1 Amps DC MAX (Opening/Closing), 0.1 mAmps MIN (1VDC, Opening/Closing)
Resistance:	300 mOhms MAX (Contact Resistance)
Miscellaneous:	Differential Temperature = 10C MAX. Contact Shape B = Break. Power = 1W DC MAX (Opening/Closing)