


KEMET, TRS



Dimensions

D	8.2mm MAX
L	50mm MAX
L2	29mm MAX
T	20mm MAX
LL	200mm

Packaging Specifications

Packaging:	Bulk, Rubber Band
Packaging Quantity:	600

General Information

Series:	TRS
Type:	Thermal Sensors
Style:	Axial
Description:	Thermal Reed Switch
Features:	BLR Series
Lead:	Cables
RoHS:	Yes
Approvals:	UL, CSA, VDE

Specifications

Rated Temperature:	60C
Rated Temperature Tolerance:	+/-2.5C
Temperature Range:	0/+130C
Voltage AC:	264 VAC MAX (Opening/Closing)
Current:	0.275 Amps MAX (Make/Break)
Miscellaneous:	Differential Temperature = 10C MAX. Power = 60.5W AC MAX (Opening/Closing)