VISIO-EYE: Digital Wi-Fi camera (C-mount) for Optical Instruments & Devices + Spacer Ring

VISIO-EYE can be mounted without additional Lens or Adapters on any trinocular optical microscope with separate camera C-Mount port.



FEATURES

- Photo & video resolution: 1.3MPx -1280x1024, 640x480, 320x240
- Frame rate: up to 30fps
- IEEE 802.11 b/g/n standards compliant
- Wireless transmission distance: up to 5m
- Frequency range: 2.400GHz ~ 2.4835GHz
- Li-ion battery: continuous working time appx. 2 hours full charging time - appx. 2 hours

- Camera sensor: CMOS 1/4"
- Lens: high definition microscopy lens
- Dimension: 36mm (Ø) x 75mm (length)
- PC interface: USB 2.0
- Mini USB cable: 1.2m
- Power consumption: max 2.5W

APPLICATIONS

- Industrial and Electronic Inspection/QC
- Education
- Research and Scientific Analysis
- **Forensics**
- Print inspection
- Textile inspection
- Trichology

- Entomology
- **Botany**
- Mineralogy
- Collectibles
- Jewelry and Watch Repair
- Reading assistance

And more ...













