



Quality Products. Service Excellence.

## Tube Axial Fans *DNMF Series*



### Features

- Choice of 4.70" (120mm), 3.15" (80mm), 5.91" (150mm) or 10" (254mm).
- Choice of either 115 or 230 VAC, 50/60 Hz.
- Impedance protected motor.
- Class-B insulated.
- Ball bearing construction, metal or plastic blades.
- Diecast aluminum body.
- DNMF100AC, FAN150AC and FAN10A fans have male plug terminations (requires fan cords).
- FAN80AC fans have 11" long lead wires.
- Fan component is recognized to UL 507 and CSA certified.
- Includes mounting hardware.



### Accessories

- Fan Cords
- Filter Fan Grills

Part No. 115 VAC	Part No. 230 VAC	Overall Dimensions			Wattage		Speed		Noise (dB)	Use With Fan Guard	Use With Filter Grill
		Height	Width	Depth	CFM	50Hz	60Hz	(RPM)		Part No.	Part No.
FAN80AC115	FAN80AC230	3.15	3.15	1.50	32	11	10	3100	34	FAN80FG	XPFA80*
DNMF100AC115	DNMF100AC230	4.70	4.70	1.50	105	24	22	3000	56	DNFG	XPFA120*
FAN150AC115	-	5.75	6.72	2.00	210	27	26	3100	63	FAN150FG	XPFA150*
-	FAN150AC230	5.90	6.72	2.20	230	46	40	3400	53	FAN150FG	XPFA150*
FAN10A115	FAN10A220	10.00 dia.	3.50	550	30	35	1650	60	60	FAN10FG	XPFA254*

Data subject to change without notice

© 2017. Hammond Manufacturing Ltd. All rights reserved.