



Quality Products. Service Excellence.

20 Amp Metered Horizontal Rackmount Outlet Strip 1589-AM Series

Front or Rear Mounted Receptacles

Features



- Designed for power distribution from the front or rear of the unit.
- Panel dimensions are 1.75" high (1U) and 19" rack width.
- Available with multi-colored on/off switch or red pilot light to indicate power on.
- Available in black powder coat finish.
- The 20 amp. series uses heavy 12 gauge wire cord - 12/3 SJT for extreme temperature ranges and integral NEMA 5-20P straight blade or L5-20P locking type molded plug.

Specifications

- Includes 20 Amp, 125 VAC circuit breaker to prevent accidental overload.
- Unit includes - easy to read 0.37" high, red LED ammeter (1.38" x 0.88" display).
- Digital ammeter accuracy +/- 0.1 Amps
- UL/cUL recognized Standard UL1363 file No. E166039 & CSA C22.2 No. 308-14



Accessories

- Mounting Hardware
- Rail Depth Adapter Kit

On/Off Switch Part No.	Illuminated Light Only Part No.	Overall Dimensions			Number of Outlets		Outlet NEMA Type	Cord Length (ft)	Plug Blade Type	NEMA Plug Type	Rack Units
		Height	Width	Depth	On Front	On Rear					
1589H6C1BKRFAM	1589T6C1BKRFAM	1.72	19.00	2.66	6	0	5-20R	6	Locking	L5-20P	1U
1589H6F1BKRFAM	1589T6F1BKRFAM	1.72	19.00	2.66	6	0	5-20R	6	Straight	5-20P	1U
1589H6C1BKRRAM	1589T6C1BKRRAM	1.72	19.00	2.66	0	6	5-20R	6	Locking	L5-20P	1U
1589H6F1BKRRAM	1589T6F1BKRRAM	1.72	19.00	2.66	0	6	5-20R	6	Straight	5-20P	1U

Data subject to change without notice

© 2017. Hammond Manufacturing Ltd. All rights reserved.