

HGA36050

PowerPact H I-Line Circuit Breaker, ThermMagn, 50A, 3P, 600V, 18kA

Product availability : Stock - Normally stocked in distribution facility



Main

| | |
|---------------------------|------------------|
| Product or component type | Circuit breaker |
| Range of product | PowerPact H |
| Trip unit technology | Thermal-magnetic |
| Breaking capacity code | G |

Complementary

| | |
|---|---|
| Line Rated Current | 50 A |
| Poles description | 3P |
| Breaking capacity | 65 kA at 240 V AC 35 kA at 480 V AC 18 kA at 600 V AC 20 kA at 500 V DC 20 kA at 250 V DC |
| System Voltage | 500 V DC 600 V AC |
| [Ics] rated service short-circuit breaking capacity | 80 % |
| Mounting mode | I-Line |
| Electrical connection | I-Line connection line Lugs load |
| AWG gauge | AWG 14...AWG 3/0 (aluminium/copper) |
| Phase connection | ABC |
| Magnetic hold current | 400 A |
| Magnetic tripping current | 850 A |

Environment

| | |
|------------------------|-----------|
| Product certifications | CSA CE |
|------------------------|-----------|

UL listed
IEC

Ambient air temperature for operation 104 °F (40 °C)

Ordering and shipping details

| | |
|-----------------------|--|
| Category | 01117 - HG, HJ, JG, JJ I-LINE BREAKER/SWITCH |
| Discount Schedule | DE2 |
| GTIN | 00785901795025 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 5.969999999999998 |
| Returnability | Y |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0832 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|