

HJL36030M71

PowerPact H Circuit Breaker, Motor Protector, 30A, 3P, 600V, 25kA

Product availability : Stock - Normally stocked in distribution facility



Main

| | |
|---------------------------|-------------------------|
| Product or component type | Motor Circuit Protector |
| Range of product | PowerPact H |
| Trip unit technology | Electronic |
| Breaking capacity code | J |

Complementary

| | |
|---|---|
| Line Rated Current | 30 A |
| Poles description | 3P |
| Breaking capacity | 65 kA at 480 V AC 25 kA at 600 V AC 100 kA at 240 V AC 20 kA at 250 V DC |
| System Voltage | 600 V AC |
| [Ics] rated service short-circuit breaking capacity | 80 % |
| Mounting mode | Unit mount |
| Electrical connection | Lugs load Lugs line |
| AWG gauge | AWG 14...AWG 3/0 (aluminium/copper) |
| [Ith] conventional free air thermal current | 1.5...25 A |
| Magnetic tripping current | 9...325 A |

Environment

| | |
|------------------------|------------------------|
| Product certifications | CCC IEC UR CE |
|------------------------|------------------------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|----------------|
| Ambient air temperature for operation | 104 °F (40 °C) |
|---------------------------------------|----------------|

Ordering and shipping details

| | |
|-----------------------|---|
| Category | 01125 - HJ, JJ UNT MNT MTR CIRCUIT PROTECTR |
| Discount Schedule | DE2 |
| GTIN | 00785901492948 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 4.379999999999999 |
| Returnability | Y |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0832 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|