

# HJL36100M73

## PowerPact H Circuit Breaker, Motor Protector, 100A, 3P, 600V, 25kA

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Motor Circuit Protector
Range of product	PowerPact H
Trip unit technology	Electronic standard
Breaking capacity code	J

### Complementary

Line Rated Current	100 A
Poles description	3P
Breaking capacity	65 kA at 480 V AC 25 kA at 600 V AC 100 kA at 240 V AC
System Voltage	600 V AC
Mounting mode	Unit mount
Electrical connection	Lugs load Lugs line
AWG gauge	AWG 14...AWG 3/0 (aluminium/copper)
[I <sub>th</sub> ] conventional free air thermal current	30...80 A
Magnetic tripping current	180...1040 A

### Environment

Product certifications	CE CCC IEC UR
Ambient air temperature for operation	104 °F (40 °C)

## Ordering and shipping details

Category	01125 - HJ, JJ UNT MNT MTR CIRCUIT PROTECTR
Discount Schedule	DE2
GTIN	00785901647706
Nbr. of units in pkg.	1
Package weight(Lbs)	4.379999999999999
Returnability	Y
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0832 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------