



Main

Product or component type	Circuit breaker
Range of product	PowerPact Q
Trip unit technology	Thermal-magnetic

Complementary

Line Rated Current	200 A
System Voltage	240 V AC
Number of poles	2
Breaking capacity	10 kA 240 V AC
[Ics] rated service short-circuit breaking capacity	50 %
Breaking capacity code	B
Mounting mode	I-Line
Electrical connection	Lugs on load: AWG 4...300 kcmil (aluminium/copper) I-Line connection on line AC connection
Phase connection	AC
Magnetic hold current	1200 A
Magnetic tripping current	2400 A

Environment

Product certifications	IEC CSA UL listed
------------------------	-------------------------

Ordering and shipping details

Category	01023 - Q2 BREAKER & SWITCH
----------	-----------------------------

Discount Schedule	DE2
GTIN	00785901672555
Nbr. of units in pkg.	1
Package weight(Lbs)	4.75
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1413 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------