

HJL36050M72

PowerPact H Circuit Breaker, Motor Protector, 50A, 3P, 600V, 25kA

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Motor Circuit Protector
Range of product	PowerPact H
Trip unit technology	Electronic
Breaking capacity code	J

Complementary

Line Rated Current	50 A
Poles description	3P
Breaking capacity	65 kA at 480 V AC 25 kA at 600 V AC 100 kA at 240 V AC
System Voltage	600 V AC
[Ics] rated service short-circuit breaking capacity	80 %
Mounting mode	Unit mount
Electrical connection	Lugs load Lugs line
AWG gauge	AWG 14...AWG 3/0 (aluminium/copper)
[Ith] conventional free air thermal current	14...42 A
Magnetic tripping current	84...546 A

Environment

Product certifications	CE IEC UR CCC
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	01125 - HJ, JJ UNT MNT MTR CIRCUIT PROTECTR
Discount Schedule	DE2
GTIN	00785901591146
Nbr. of units in pkg.	1
Package weight(Lbs)	4.379999999999999
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0832 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------