




The supplier acknowledges that, with the acceptance of the drawing, he is in a position to manufacture the illustrated part in accordance with the drawing in reproducible form and series production. Through the selected manufacturing processes no impairments will arise in the material and structure which could subsequently lead to an impairment of the component. Verbal agreements over and above that are not valid. Deviations from this rule must be written and must be signed by the purchaser.

This drawing may not be copied, reproduced or made available to third parties in any way whatsoever without or prior written approval.

M/ Scale 1:5



ON
OFF



Adresse (2:1) gegenüber dem Logo/
address (2:1) opposite to the logo

ANSMANN AG 97959 Assamstadt
Industriestr. 10 Germany
Art.-Nr.: 5000023

- Technische Daten/ :
technical data
- Leuchtmittel/ : LED
illuminant
- Zellenzahl/ : 3x Knopfzellen LR 41 1,5V
number of cells : 3x button cells LR 41 1,5V
- Gehäusefarbe/ : silber / silver
color of case
- Gewicht/ : 63g inkl. Verpackung / incl. package
weight
- Verpackung/ : Blisterverpackung 95x23x255mm (LxBxH) VE: 10 Stück
package : blister package 95x23x255mm (LxWxH) PU: 10 psc.
- Approbation/ : CE
approval

Bedruckung 2:1/
printing 2:1



Application range for inquiry			Allowable deviation general tolerances		Surface	Model:	Material:	
			DIN ISO 2768-m			Scale (DIN A4): 1:1		Weight:
V6	adress added	19.01.15	SIT	2005	Date	Name	Drawing name	
V5	packing dimensions updated	13.06.07	SP	Drawn by	04.02	SP	SF-1 Zeigestab mit LED/ SF-1 search stick with LED	
V4	printing, LED head modified	13.06.07	OB	Approved by				
V3	printing, LED head modified	07.03.07	SP				Drawing number	
V2	package dimensions updated	29.09.06	OB				Part number	
V1	package dimensions updated	16.05.06	SP				5000023	
V0	package, weight updated	31.05.05	SP				Sheet	
V0	---	04.02.05	SP				1/1	
Version	Change	Date	Name	Project: xx-xxxx-xxxx		Replaced by:	Replacement through:	