

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1720650306](#)
Status: **Active**
Overview: [Mega-Fit Power Connectors](#)
Description: Mega-Fit Slim Vertical Header, Through Hole, 5.70mm Pitch, Dual Row, 6 Circuits, 0.76µm Gold (Au) Plating, Glow Wire Capable, Black

Documents:

Drawing (PDF)	Packaging Specification 768291100-000 (PDF)
Product Specification PS-76823-100-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification TS-76823-100-001 (PDF)	Product Literature (PDF)
Application Specification AS-76823-100-001 (PDF)	

General

Product Family	PCB Headers
Series	172065
Application	Power, Wire-to-Board
Overview	Mega-Fit Power Connectors
Product Literature Order No	987650-5401
Product Name	Mega-Fit
UPC	889056897297

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Glow-Wire Compliant	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Mated Height	16.78mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	3.453/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.73mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm
Packaging Type	Tray
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +120°C
Termination Interface: Style	Through Hole
Unmated Height	14.80mm

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[172065](#) Series

Mates With

Mega-Fit Receptacle Housing [171692](#) ,
[170001](#)

Current - Maximum per Contact
Voltage - Maximum

23.0A
600V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification
Packaging Specification
Product Specification
Sales Drawing

AS-76823-100-001
768291100-000
PS-76823-100-001, TS-76823-100-001
768290002-000

This document was generated on 11/03/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION