


DATA SHEET	44423241
EPIC® MHB 24 R Multi-frame	Valid from: 24.05.2017

Description

- Multi- frame for recording own and third-party modules
- EPIC® MH system is pluggable with the market standard
- The mixing of various functions in one connector ensures a high degree of flexibility
- PE Connection from 1mm² to 6mm² with wire end ferrule, 10mm² with adapter
- Use for railway applications -Brand protection in rail vehicles: test according to EN 45545-2. Requirement sentences R22 and R23. Hazard levels HL1, HL2 and HL3



General Characteristics

Product description	EPIC® MHB 24 R (a, b, c, d, e, f)
Series	MH Multi-frame
Version	Female
Number of Modules	6

Surfaces



Frame	Zinc die casting alloy
-------	------------------------

Standard

Certificated	IEC 61984
--------------	-----------

DATA SHEET	44423241
EPIC® MHB 24 R Multi-frame	Valid from: 24.05.2017

Technical Drawing



Automation



Industrial machinery and plant engineering



Wind Energy

Info

Frame system for modules

Various functions can be used together in one connector

Product features

The MCR "male" frame version is designed for use with modules with male contacts; the "female" version is designed for use with modules with female contacts. The high design is to be used for sleeve housings

Remark

Photographs are not to scale and do not represent detailed images of the respective products.