

# **EPIC® MH 4.0mm Contacts**

High flexibility by the use of any combination of inserts in one connector

### Info

Stamped gold plated contacts with 0.8mm diameter for D-Sub inserts





Robust



Wind Energy



Rail



Mechanical and plant engineering



Automation & amp; fältinstallation

### **Benefits**

Crimp connection for permanent vibration proof contact EPIC® MH system is mateable with the market standard

## **Application range**

Mechanical engineering Robotics industry Plant engineering Renewable energy Railway applications / vehicle construction





# **EPIC® MH 4.0mm Contacts**

**Technical Data** 

Classification: ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Contact resistance: < 5 mOhm

Termination methods: Crimp termination: 1.5 mm<sup>2</sup> - 10 mm<sup>2</sup>

Stripping length (mm): 10

Cycle of mechanical operation: 500

### Note

Photographs are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.



# **EPIC® MH 4.0mm Contacts**

Article number	Article description	Contact type	Connection cross section (mm²)
44423250	EPIC® MH SCEM AG 1.5sqmm D=4.0	male	1.5
44423255	EPIC® MH BCEM AG 1.5sqmm D=4.0	female	1.5
44423251	EPIC® MH SCEM AG 2.5sqmm D=4.0	male	2.5
44423256	EPIC® MH BCEM AG 2.5sqmm D=4.0	female	2.5
44423252	EPIC® MH SCEM AG 4sqmm D=4.0	male	4
44423257	EPIC® MH BCEM AG 4sqmm D=4.0	female	4
44423253	EPIC® MH SCEM AG 6sqmm D=4.0	male	6
44423258	EPIC® MH BCEM AG 6sqmm D=4.0	female	6
44423254	EPIC® MH SCEM AG 10sqmm D=4.0	male	10
44423259	EPIC® MH BCEM AG 10sqmm D=4.0	female	10