# Product Specifications





# 2111122-1

SL Series Coupler, category 5e, inline, shielded

# **Product Classification**

Portfolio NETCONNECT®

Product Series SL Series

Product Type Modular jack coupler

Regional Availability Asia | Latin America | North America

### **Body Features**

Body Style Inline

# **Configuration Features**

Keyed No Number of Positions 8

Wiring Pattern One-to-one

#### **Contact Features**

Contact Base Material Phosphor bronze

Contact Mating Area Plating Material Gold

#### **Dimensions**

Panel Thickness, recommended 1.57 mm | 0.06 in

### **Electrical Characteristics**

Contact Resistance 20 m Ohms
Insulation Resistance 500 MO
Voltage Rating 150 Vac

# **Housing Features**

Housing Color Silver gray

# **Industry Standards**

Approved Standards ANSI/TIA-568-C.2 | IEC 60603-7

UL Flammability Rating UL 94V-0

# Product Specifications



2111122-1

# **Mechanical Attachment**

Coupler Style Jack

Mount Cutout Dimensions .582 x .790 in | 14.78 x 20.07 mm

# **Operation/Application**

Plug Insertion Cycles (Min) 750 cycles

## **Packaging Features**

Packaging Method Bag/Box Packaging Quantity 25

# **Product Type Features**

Performance Category Category 5e Shielded Yes

Coupler Type MJ/MJ

## **Usage Conditions**

Operating Temperature -10 - 60 °C | 14 - 140 °F

Relative Humidity (Operating) 10 – 90 %

# **Regulatory Compliance/Certifications**

AgencyClassificationRoHS 2011/65/EUCompliant